

Ceiling mounted • Dry location listed



Description:

This energy efficient and lightweight 52" fan offers clean lines and a design that complements modern interiors. Edgefield features an updated and stylish shell-shaped blade holder that contains five sweeping blades. A four-speed pull chain and a manual reverse switch come standard with design.

Specifications:

- Architectural Bronze (-129) (painted)
- Steel construction
- The 52" Edgefield features an updated and stylish shell-shaped blade holder containing five sweeping blades
- Energy Star rated
- Powerful and quiet DC Motor
- Reversible Classic Walnut and Medium Cherry blades
- Rich Architectural Bronze finish
- Beautiful and expansive in design, the indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- Features a dual mount system and a four-speed pull chain fan switch
- Brass four speed pull chain
- The design features clean, precise fittings and lends itself to Transitional, Contemporary and Farmhouse décor
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges from 226- to 400-square feet
- Compatible with universal light kits
- A 1" x 6" downrod is included. Longer accessory downrods can be ordered separately
- UL dry location listed
- Limited Lifetime Warranty
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting bracket for outlet box included
- 80" of wire supplied
- Classic Walnut/Medium Cherry reversible blades, mdf construction
- Brass pull chain with Walnut fob
- 13 degree blade pitch
- 4 Speed, Manual Reverse
- ENERGY STAR® qualified
- Airflow: 5741 CFM*
- Energy consumption: 33 watts (excluding lights)*
- Airflow efficiency: 171 cfm/watt*
- * Fan on a downrod

Performance:

Input Voltage	120 V
Input Frequency	60 Hz
Warranty	Limited Lifetime
Labels	ULus Dry location listed
	ENERGY STAR® qualified

P250016-129

Images:



Dimensions:

Diameter: 52"
Height: 14-5/8"

