

# Chapin

Ceiling Mounted • Dry Location Listed

## Description:

This ceiling fan effortlessly unites a spacious room, creating an atmosphere that's both relaxing and reviving. Four plywood blades attach to a dual mount canopy. The fixture features a oil graphite finish for a design destined to provide a truly relaxing experience.

## Specifications:

- Four plywood blades.
- The fixture features a graphite finish for a design destined to provide a truly relaxing experience.
- This ceiling fan effortlessly unites a spacious room, creating an atmosphere that's both relaxing and reviving.
- Ideal for any living room, great room, or bedroom.
- Light kit adaptable.
- Measures 56-inch width by 15-7/8-inch height.
- Light kit not included.
- Remote control included.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.
- Canopy covers a standard 4" recessed outlet box: 5.19 in W., 2.19 in ht., 5.19 in depth
- 80 in of wire supplied

## Performance:

Input Voltage	120 V
Input Frequency	60 Hz
Warranty	Limited Lifetime Warranty
Labels	UL Dry Location Listed
	AC motor

# P250022-143



## Dimensions:

Diameter: 56 in  
Height: 15-7/8 in

