

Project:	
Fixture Type:	

Location:

Contact:

Bedwin

Ceiling Mounted • Dry Location Listed

Description:

Recall charming, rustic lattice work with this farmhouse-inspired ceiling fan. Four rough hewn plywood blades take center stage in the design. With a beautiful galvanized finish, this ceiling fan is sure to help transform any living space into a cool paradise of relaxation.

Specifications:

- Four rough hewn plywood blades take center stage in the design.
- With a beautiful galvanized finish, this ceiling fan is sure to help transform any living space into a cool paradise of relaxation.
- Recall charming, rustic lattice work with this farmhouse-inspired ceiling fan.
- $\boldsymbol{\cdot}$ Ideal for any living room, great room, or bedroom.
- $\cdot\,$ Perfect for farmhouse and rustic settings.
- Measures 56-inch width by 15-3/8-inch height.
- Light kit not included
- Light kit adaptable.
- Remote control included.
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.
- Canopy covers a standard 4" recessed outlet box: 5.13 in W., 2.19 in ht., 5.13 in depth
- 80 in of wire supplied

Performance:

Input Voltage	120 V
Input Frequency	60 Hz
Warranty	Limited Lifetime Warranty
Labels	cULus Dry Location Listed
	DC motor





P250024-141

Dimensions:

Diameter: 56 in Height: 15-3/8 in

