

# Lindale

Ceiling Mounted • Dry Location Listed

### Description:

Retreat for a little rest and relaxation under the gentle airflow offered by this ceiling fan. A flush mount design anchors four rectangular plywood blades as they attach to the vase-inspired center. The ceiling fan is coated in a satin white finish complemented by understated silver accents.

### Specifications:

- A flush mount design anchors four rectangular plywood blades as they attach to the vase-inspired center.
- The ceiling fan is coated in a satin white finish complemented by understated silver accents.
- Retreat for a little rest and relaxation under the gentle airflow offered by this ceiling fan.
- Ideal for any living room, great room, or bedroom.
- Perfect for mid-century modern, modern, or transitional settings.
- Measures 52-inch width by 11-3/16-inch height.
- Light kit available (P2669).
- Remote control included.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.
- Canopy covers a standard 4" recessed outlet box: 7.05 in W., 0.675 in ht., 7.05 in depth
- 12 in of wire supplied

### Performance:

Input Voltage	120 V
Input Frequency	60 Hz
Warranty	Limited Lifetime Warranty
Labels	UL Dry Location Listed
	AC motor

# P250028-028



### Dimensions:

Diameter: 52 in  
Height: 11-3/16 in

## ENERGYGUIDE

Estimated  
Yearly Energy Cost

# \$11

\$3

▼

\$34

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day  
 • Your cost depends on rates and use  
 • Energy Use: 39 Watts

Airflow

# 3,366

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move  
 • Airflow Efficiency: 87 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights fic.gov/energy