

Project:	
Fixture Type:	

Location:

Contact:

Lindale

Ceiling Mounted • Dry Location Listed

Description:

Retreat for a little rest and relaxation under the gentle airflow offered by this ceiling fan. A flush mount design anchors four rectangular plywood blades as they attach to the vase-inspired center. The ceiling fan is coated in an antique nickel finish.

Specifications:

- A flush mount design anchors four rectangular plywood blades as they attach to the vase-inspired center.
- The ceiling fan is coated in an antique nickel finish.
- Retreat for a little rest and relaxation under the gentle airflow offered by this ceiling fan.
- Ideal for any living room, great room, or bedroom.
- Perfect for mid-century modern, modern, or transitional settings.
- Measures 52-inch width by 11-3/16-inch height.
- Light kit available (P2669).
- Remote control included.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.
- Canopy covers a standard 4" recessed outlet box: 7.05 in W., 0.675 in ht., 7.05 in depth
- + 12 in of wire supplied

Performance:

Input Voltage	120 V
Input Frequency	60 Hz
Warranty	Limited Lifetime Warranty
Labels	UL Dry Location Listed
	AC motor





P250028-081

Dimensions:

Diameter: 52 in Height: 11-3/16 in

