

Huff

Ceiling Mounted • Damp Location Listed

Description:

The hassles and headaches of the day fade away under the relaxing airflow created by this ceiling fan. Six expansive aluminum blades with decorative winglets stretch out from the center. The fan is coated in a brushed nickel finish with complementary highlights to create a perfect design for your home.

Specifications:

- Six expansive aluminum blades with decorative winglets stretch out from the center.
- The fan is coated in a brushed nickel finish with complementary highlights to create a perfect design for your home.
- The hassles and headaches of the day fade away under the relaxing airflow created by this ceiling fan.
- Ideal for any living room, bedroom, covered porch or patio.
- Perfect for modern or transitional settings.
- Measures 96-inch width by 15-7/16-inch height.
- Light kit not included
- Light kit adaptable.
- Remote control included.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.
- Canopy covers a standard 4" recessed outlet box: 6.125 in W., 2.5 in ht., 6.125 in depth
- 80 in of wire supplied

Performance:

Input Voltage	120 V
Input Frequency	60 Hz
Warranty	Limited Lifetime Warranty
Labels	cULus Damp Location Listed
	DC motor

P250030-009



Dimensions:

Diameter: 96 in
Height: 15-7/16 in

