PROGRESS LIGHTING[™]

Project:

Fixture Type:

Location

Contact:

Braden

Description:

Experience an ideal blend of style and function with the Braden Collection 44-Inch 3-Blade Matte White LED Mid-Century Modern Indoor Hugger Ceiling Fan. Three reversible plywood blades are coated in white and natural cherry finishes for extra design versatility. The fan's center is coated in a crisp matte white finish to accentuate its modern character. A remote control with batteries is included so you can adjust full-range dimming and fan speed without breaking a sweat.

Specifications:

- White Opal Glass Bowl
- Application: Ideal for any bedroom, great room, living room, or sitting room.
- Style: Perfect for mid-century modern, modern, and transitional style settings.
- Blades: Three reversible plywood blades are coated in white and natural cherry finishes for extra design versatility.
- · Dimensions: Measures 44-inch width by 9.8125-inch height.
- Remote: A remote control with batteries is included so you can adjust full-range dimming and fan speed without breaking a sweat.
- Lighting: For ideal illumination, a dimmable LED module light source is included (18w, 3000K, 90CRI). A white opal glass shade covers the light source.
- Room Size: Light experts recommend installing this fan in a room size that ranges from 226 to 400-square feet. Great for rooms with low ceiling heights.
- Certifications: Certifications include cULus dry location listed, Title 20, Title 24.
- Pairs With: Pairs with a variety of decorative fixtures from Progress Lighting.
- Warranty: Our Limited Lifetime Warranty guarantees your complete satisfaction with your purchase and we offer professional after-sales customer service support.
- Dimmable to 10% brightness (See Dimming Notes)
- covers a standard 4" recessed outlet box
- + 10 in of wire supplied

Performance:

Number of Modules	1
Input Power	18 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,600/88 (LM-79)
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime Warranty
Labels	cULus Dry Location Listed
	Meets California Title 24 JA8-2016

P250058-028-30

Dry Location Listed PROGRESS LED






Dimensions:

Length: 44 in Diameter: 44 in Height: 9-13/16 in

White Opal Glass Bowl Width: 6 in Height: 1-1/2 in





Braden

Dimming Notes:

P250058-028-30 is designed to be compatible with many Triac/ELV controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

IDevices_IDEV009	
Leviton_6672	
Leviton_6674	
Lutron_NTEVL-300	
Lutron_DVELV-300P	
Lutron_DVCL-253P	
Lutron_Caseta Wireless	
Lutron_AYCL-153P	
Lutron_TGCL-153-PH-WH	

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

• Dry Location Listed PROGRESS LED

P250058-028-30