

roject.
ixture Type:
ocation:

Ryne

• Damp Location Listed PROGRESS LED

Description:

Enjoy a beautiful ceiling fan at a fantastic price with the Ryne Collection 52-Inch 3-Blade Matte White LED Transitional Indoor/Outdoor Ceiling Fan. Three slightly curved ABS blades are coated in a crisp matte white finish that will complement a variety of living areas. The blades are resistant to warping from environmental conditions and offer a long product lifespan. The fan's downrod and canopy are coated in a white finish to complete the transitional design. A 6-speed full-function remote control with batteries is included so you can adjust full-range dimming and fan speed without breaking a sweat.

Specifications:

- · Application: Ideal for any bedroom, living room, great room, or covered porch.
- · Style: Perfect for transitional style settings.
- Blades: Three slightly curved ABS blades are coated in a crisp matte white finish that will
 complement a variety of living areas. Blades are resistant to warping from environmental
 conditions.
- · Dimensions: Measures 52-inch width by 13.5-inch height.
- Remote: A 6-speed full-function remote control with batteries is included so you can adjust full-range dimming and fan speed without breaking a sweat. Add the P2673-01 WIFI module to the fan for added flexibility control.
- Lighting: For ideal illumination, an integrated LED module light source is included (18w, 3000K, 90 CRI). The light source is covered by a shatterproof white opal shade.
- Accessories: A downrod and canopy are also included. Longer downrods can be ordered separately.
- · Certifications: Certifications include cETLus damp location listed, Title 20, Title 24.
- · Pairs With: Pairs with a variety of decorative fixtures from Progress Lighting.
- Warranty: Our Limited Lifetime Warranty guarantees your complete satisfaction with your purchase and we offer professional customer service support.
- Dimmable to 10% brightness (See Dimming Notes)
- · Canopy covers a standard 4" recessed outlet box: 7 W., 2.5 ht., 7 depth
- 80 in of wire supplied

Performance:

1
18 W
120 V
60 Hz
1,600/88 (LM-79)
90 CRI
50000 (L70/TM-21)
FCC Title 47, Part 15, Class B
Limited Lifetime Warranty
cETLus Damp Location Listed
Meets California Title 24 JA8-2016

P250060-028-30



Contact:



Dimensions:

Length: 52 in Diameter: 52 in Height: 13-1/2 in

Shatterproof White Lens

Width: 5-1/27 in Height: 1.3 in

