

Project:			
Fixture Type:			
Location:			
Contact:			

Springer

Ceiling downrod Mounted • Dry Location Listed

Description:

Springer Collection 52-Inch Antique Nickel 12-Blade DC Motor Windmill Ceiling Fan

Specifications:

- · Canopy covers a standard 4" recessed outlet box: 6 in W., 2.25 in ht., 6 in depth
- · Mounting Bracket
- 80 in of wire supplied

Performance:

Input Voltage	120 V
Input Frequency	60 Hz
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime warranty
Labels	cETLus Dry Location Listed
	DC motor



Dimensions:

Length: 52 in Diameter: 52 in Height: 17-3/8 in

