

# Springer

Ceiling downrod Mounted • Dry Location Listed

### Description:

Springer Collection 52-Inch 12-Blade Architectural Bronze DC Motor Farm-house Windmill Ceiling Fan

### Specifications:

- Canopy covers a standard 4" recessed outlet box: 6 in W., 2.25 in ht., 6 in depth
- Mounting Bracket
- 80 in of wire supplied

### Performance:

Input Voltage	120 V
Input Frequency	60 Hz
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime warranty
Labels	cETLus Dry Location Listed
	DC motor

# P250065-129



### Dimensions:

Length: 52 in  
 Diameter: 52 in  
 Height: 17-3/8 in

## ENERGYGUIDE

**Estimated  
Yearly Energy Cost**

# \$5

\$3

\$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6.4 hours use per day
- Your cost depends on rates and use
- Energy Use: 19 Watts

**Airflow**

# 4,632

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 245 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy