

Springer

Ceiling downrod Mounted • Dry Location Listed

Description:

Springer Collection 52-Inch Matte Black 12-Blade DC Motor Windmill Ceiling Fan

Specifications:

- Canopy covers a standard 4" recessed outlet box: 6 in W., 2.25 in ht., 6 in depth
- Mounting Bracket
- 80 in of wire supplied

Performance:

Input Voltage	120 V
Input Frequency	60 Hz
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime warranty
Labels	cETLus Dry Location Listed
	DC motor

P250065-31M



Dimensions:

Length: 52 in
 Diameter: 52 in
 Height: 17-3/8 in

ENERGYGUIDE

**Estimated
Yearly Energy Cost**

\$5

\$3

▼

\$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6.4 hours use per day
- **Your cost depends on rates and use**
- Energy Use: 19 Watts

Airflow

4,632

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 245 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy