

## AirPro

Ceiling downrod Mounted • Dry Location Listed

### Description:

AirPro 52-Inch Brushed Nickel 5-Blade AC Motor Traditional Ceiling Fan

### Specifications:

- Canopy covers a standard 4" recessed outlet box: 5.875 in W., 2.5 in ht., 5.875 in depth
- Mounting Bracket
- 80 in of wire supplied

### Performance:

Input Voltage	120 V
Input Frequency	60 Hz
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime warranty
Labels	UL Dry Location Listed
	AC motor

# P250066-009



### Dimensions:

Diameter: 52 in  
Height: 13-1/2 in

