

|--|

Fixture Type:

Location:

Contact:

## Briarwood

### Ceiling downrod Mounted • Damp Location Listed

#### **Description:**

Briarwood Collection 22-Inch 3-Blade Graphite AC Motor Farmhouse Ceiling Fan

#### **Specifications:**

- Fully dimmable with dimmable bulbs
- Canopy covers a standard 4" recessed outlet box: 7.25 in W., 2 in ht., 7.25 in depth
- Mounting Bracket
- + 45 in of wire supplied

#### **Performance:**

Number of Lamps	4
Input Power	5.5 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	500/90 (LM-79)
CCT	2200 К
CRI	80 CRI
Life (hours)	15000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime warranty
Labels	cETLus Damp Location Listed
	AC motor

# P250067-143-WB



#### **Dimensions:**

Length: 22 in Depth: 22 in Height: 17 in

