

Project:
Fixture Type:
Location:

Briarwood

Ceiling downrod Mounted • Damp Location Listed

Contact:

Description:

Briarwood Collection 22-Inch 3-Blade Matte Black AC Motor $\,$ Farmhouse Ceiling Fan

Specifications:

- · Fully dimmable with dimmable bulbs
- · Canopy covers a standard 4" recessed outlet box: 7.25 in W., 2 in ht., 7.25 in depth
- · Mounting Bracket
- · 45 in of wire supplied

Performance:

Number of Lamps	4
Input Power	5.5 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	500/90 (LM-79)
CCT	2200 K
CRI	80 CRI
Life (hours)	15000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime warranty
Labels	cETLus Damp Location Listed
	AC motor

P250067-31M-WB



Dimensions:

Length: 22 in Depth: 22 in Height: 17 in

