

|--|

-----

Fixture Type:

Location:

Contact:

## Belva

### Ceiling downrod Mounted • Damp Location Listed

#### **Description:**

Belva Collection 25.25-Inch 3-Blade Cottage White AC Motor Coastal Ceiling Fan

#### **Specifications:**

- Fully dimmable with dimmable bulbs
- Canopy covers a standard 4" recessed outlet box: 7.25 in W., 2 in ht., 7.25 in depth
- Mounting Bracket
- + 45 in of wire supplied

#### **Performance:**

Number of Lamps	4
Input Power	5.5 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	500/90 (LM-79)
ССТ	2200 K
CRI	80 CRI
Life (hours)	15000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime warranty
Labels	cETLus Damp Location Listed
	AC motor

# P250068-151-WB



#### **Dimensions:**

Length: 25-1/4 in Diameter: 25-1/4 in Height: 17-7/8 in

