

Belva

Ceiling downrod Mounted • Damp Location Listed

Description:

Belva Collection 25.25-Inch 3-Blade Matte Black AC Motor Coastal Ceiling Fan

Specifications:

- Fully dimmable with dimmable bulbs
- Canopy covers a standard 4" recessed outlet box: 7.25 in W., 2 in ht., 7.25 in depth
- Mounting Bracket
- 45 in of wire supplied

Performance:

Number of Lamps	4
Input Power	5.5 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	500/90 (LM-79)
CCT	2200 K
CRI	80 CRI
Life (hours)	15000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime warranty
Labels	cETLus Damp Location Listed
	AC motor

P250068-31M-WB



Dimensions:

Length: 25-1/4 in
 Diameter: 25-1/4 in
 Height: 17-7/8 in

ENERGYGUIDE

**Estimated
Yearly Energy Cost**

\$9

\$3

▼

\$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6.4 hours use per day
- **Your cost depends on rates and use**
- Energy Use: 30 Watts

Airflow

1,124

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 37 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy