

Project:

Fixture Type:

Location:

Contact:

Manvel

Ceiling Mounted • Damp Location Listed

Description:


Manvel offers modern elegance in a sleek form. This 60-inch ceiling fan with an energy-efficient DC motor is rated for indoor and outdoor applications. Three hand-finished, premium construction ABS blades create a stylish look that makes the ceiling fan an ideal centerpiece for living rooms, great rooms, or an outdoor covered porch. Includes a six-speed full-function remote control. Not compatible with light kits.

Specifications:

- · Ideal for a great room, living room, or outdoor covered porch
- · Perfect for urban industrial style settings
- $\cdot\,$ 3 hand-finished ABS blades coated in a walnut finish with handsome antique bronze accents
- Not compatible with light kits
- · Includes a 6-speed full-function handheld remote control
- Energy-efficient DC motor
- Measures 60-inch diameter by 11-1/4-inch height
- Includes one 4-1/2-inch down rod to adjust for a variety of ceiling heights
- Certifications/Ratings: ETLus, Damp Location Listed, Title 20
- Our Limited Lifetime Warranty guarantees your complete satisfaction with your purchase and includes professional after-sales customer service
- · Canopy covers a standard 4" recessed outlet box: 6.25 in W., 2 in ht., 6.25 in depth
- Mounting Bracket
- 80 in of wire supplied

Performance:

Input Voltage 120 VAC Warranty Limited Lifetime Warranty ETLus Damp Location Listed DC motor





P250069-020

Dimensions:

Diameter: 60 in Height: 11-1/4 in