

Manvel

Ceiling Mounted • Damp Location Listed

P250069-081

Description:

Manvel offers modern elegance in a sleek form. This 60-inch ceiling fan with an energy-efficient DC motor is rated for indoor and outdoor applications. Three hand-finished, premium construction ABS blades create a stylish look that makes the ceiling fan an ideal centerpiece for living rooms, great rooms, or an outdoor covered porch. Includes a six-speed full-function remote control. Not compatible with light kits.

Specifications:

- Ideal for a great room, living room, or outdoor covered porch
- Perfect for urban industrial style settings
- 3 hand-finished ABS blades coated in an antique wood finish with antique nickel accents
- Not compatible with light kits
- Includes a 6-speed full-function handheld remote control
- Energy-efficient DC motor
- Measures 60-inch diameter by 11-1/4-inch height
- Includes one 4-1/2-inch down rod to adjust for a variety of ceiling heights
- Certifications/Ratings: ETLus, Damp Location Listed, Title 20
- Our Limited Lifetime Warranty guarantees your complete satisfaction with your purchase and includes professional after-sales customer service
- Canopy covers a standard 4" recessed outlet box: 6.25 in W., 2 in ht., 6.25 in depth
- Mounting Bracket
- 80 in of wire supplied

Performance:

Input Voltage	120 VAC
Warranty	Limited Lifetime Warranty
Labels	ETLus Damp Location Listed
	DC motor



Dimensions:

Diameter: 60 in
 Height: 11-1/4 in

ENERGYGUIDE

Estimated Yearly Energy Cost

\$4.0

\$3 | | | \$34

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day
 • Your cost depends on rates and use
 • Energy Use: 13 Watts

Airflow

4,152

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
 • Airflow Efficiency: 310 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy