

# Manvel

Ceiling Mounted • Damp Location Listed

### Description:

Manvel Collection 60 in. Three-Blade Cottage White Urban Industrial Ceiling Fan with Full function 6 speed remote Remote Control with batteries

### Specifications:

- Canopy covers a standard 4" recessed outlet box: 6.25 in W., 2 in ht., 6.25 in depth
- Mounting Bracket
- 80 in of wire supplied

### Performance:

Input Voltage	120 VAC
Input Frequency	60 Hz
Warranty	Limited Lifetime Warranty
Labels	ETLus Damp Location Listed
	DC motor

# P250069-151



### Dimensions:

Diameter: 60 in  
 Height: 11-1/4 in

## ENERGYGUIDE

**Estimated**  
Yearly Energy Cost  
**\$4.0**

▼

\$3 | | | \$34

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day  
 • **Your cost depends on rates and use**  
 • Energy Use: 13 Watts

**Airflow**  
**4,152**  
Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move  
 • Airflow Efficiency: 310 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy