

Kennedale

Ceiling Mounted • Damp Location Listed

Description:

Kennedale is the perfect ceiling fan for cooling large spaces inside or out. Classically-styled with UV-protected, faux wood-finished reversible blades, Kennedale offers a substantial look for traditional and transitional style settings with an open floor plan or large porch. The 72-inch damp-rated DC motor fan includes a six-speed full-function handheld remote. Compatible with a universal light kit.

Specifications:

- Ideal for a great room or porch
- Perfect for transitional and traditional style settings
- 5 reversible plywood UV-protected blades coated in a driftwood or matte white finish with crisp satin white accents
- Compatible with a universal light kit (not included)
- Includes a 6-speed full-function handheld remote control with light control capabilities
- Energy-efficient DC motor
- Measures 72-inch diameter by 18-inch height
- Includes one 6-inch down rod to adjust for a variety of ceiling heights
- Certifications/Ratings: ETLus, Damp Location Listed, Title 20
- Our Limited Lifetime Warranty guarantees your complete satisfaction with your purchase and includes professional after-sales customer service
- Canopy covers a standard 4" recessed outlet box: 6.3 in W., 2 in ht., 6.3 in depth
- Mounting Bracket
- 80 in of wire supplied

Performance:

Input Voltage	120 VAC
Warranty	Limited Lifetime Warranty
Labels	ETLus Damp Location Listed
	DC motor

P250070-028



Dimensions:

Diameter: 72 in
Height: 18 in

ENERGYGUIDE	
<p>Estimated Yearly Energy Cost</p> <p>\$6.0</p> <p>\$3 \$34</p> <p>Cost Range of Similar Models (19" – 84")</p> <p>• Based on 12 cents per kWh and 6.4 hours use per day • Your cost depends on rates and use • Energy Use: 21 Watts</p>	<p>Airflow</p> <p>6,279</p> <p>Cubic Feet Per Minute</p> <p>• The higher the airflow, the more air the fan will move • Airflow Efficiency: 293 Cubic Feet Per Minute Per Watt</p>
<p>All estimates based on typical use, excluding lights ftc.gov/energy</p>	