

Project:
Fixture Type:
Location:

Kennedale

Ceiling Mounted · Damp Location Listed

Contact:

Description:

Kennedale is the perfect ceiling fan for cooling large spaces inside or out. Classically-styled with UV-protected, faux wood-finished reversible blades, Kennedale offers a substantial look for traditional and transitional style settings with an open floor plan or large porch. The 72-inch damp-rated DC motor fan includes a six-speed full-function handheld remote. Compatible with a universal light kit.

Specifications:

- · Ideal for a great room or porch
- · Perfect for transitional and traditional style settings
- 5 reversible plywood UV-protected blades coated in a grey weathered wood or silver finish with painted nickel accents
- · Compatible with a universal light kit (not included)
- · Includes a 6-speed full-function handheld remote control with light control capabilities
- · Energy-efficient DC motor
- · Measures 72-inch diameter by 18-inch height
- Includes one 6-inch down rod to adjust for a variety of ceiling heights
- · Certifications/Ratings: ETLus, Damp Location Listed, Title 20
- Our Limited Lifetime Warranty guarantees your complete satisfaction with your purchase and includes professional after-sales customer service
- Canopy covers a standard 4" recessed outlet box: 6.3 in W., 2 in ht., 6.3 in depth
- · Mounting Bracket
- 80 in of wire supplied

Performance:

Input Voltage	120 VAC
Warranty	Limited Lifetime Warranty
Labels	ETLus Damp Location Listed
	DC motor

P250070-152





Dimensions:

Diameter: 72 in Height: 18 in

