

Project:
Fixture Type:
Location:

Kasota

• Damp Location Listed PROGRESS LED

Description:

Kasota Collection 56-Inch Three-Blade Tan Linen/Oil Rubbed Bronze LED DC Motor Modern Ceiling Fan

Specifications:

- · Frosted Glass Bowl
- · Dimmable to 10% brightness (See Dimming Notes)
- · Canopy covers a standard 4" recessed outlet box: 6 in W., 2.5 in ht., 6 in depth
- · Mounting Plate
- 80 in of wire supplied

Performance:

Number of Modules	1
Input Power	18 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,400
ССТ	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime Warranty
Labels	UL Damp Location Listed
	Meets California Title 24 JA8-2016
	DC motor

P250072-108-30




Dimensions:

Contact:

Diameter: 56 in Height: 15 in

Frosted Glass Bowl Width: 6-1/2 in Height: 2-1/4 in





Kasota

• Damp Location Listed PROGRESS LED

Dimming Notes:

P250072-108-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Eaton AAL06
IDevices IDEV009
Leviton 6681
Leviton 6672
Leviton 6674
Lutron NTEVL-300
Lutron DVELV-300P
Lutron DVCL-253P
Lutron AYCL-153P
Lutron SCL-153P
Lutron TGCL-153-PH-WH

Lutron MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P250072-108-30