

Project:

Fixture Type:

Location:

Contact:

Kasota

• Damp Location Listed PROGRESS LED

Description:

Kasota Collection 56-Inch Three-Blade Charcoal Linen/Graphite LED DC Motor Modern Ceiling Fan

Specifications:

- · Frosted Glass Bowl
- · Dimmable to 10% brightness (See Dimming Notes)
- · Canopy covers a standard 4" recessed outlet box: 6 in W., 2.5 in ht., 6 in depth
- · Mounting Plate
- 80 in of wire supplied

Performance:

Number of Modules	1
Input Power	18 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,400
ССТ	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime Warranty
Labels	UL Damp Location Listed
	Meets California Title 24 JA8-2016
	DC motor


P250072-143-30



Dimensions:

Diameter: 56 in Height: 15 in

Frosted Glass Bowl Width: 6-1/2 in Height: 2-1/4 in





Kasota

• Damp Location Listed PROGRESS LED

Dimming Notes:

P250072-143-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Eaton AAL06

IDevices IDEV009

Leviton 6681

Leviton 6672

Leviton 6674

Lutron NTEVL-300

Lutron DVELV-300P

Lutron DVCL-253P

Lutron AYCL-153P

Lutron SCL-153P

Lutron TGCL-153-PH-WH

Lutron MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P250072-143-30