

Project:
Fixture Type:
Location:

Carrollwood

• Dry Location Only PROGRESS LED

Description:

Carrollwood Collection 56-Inch Reversible Six-Blade Matte Black/ Chestnut LED DC Motor Contemporary Ceiling Fan

Specifications:

- · White Opal Polycarbonate Light Cover
- · Dimmable to 10% brightness (See Dimming Notes)
- · Canopy covers a standard 4" recessed outlet box: 6 in W., 2.5 in ht., 6 in depth
- · Mounting Plate
- 80 in of wire supplied

Performance:

Number of Modules	1
Input Power	18 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,400
ССТ	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime Warranty
Labels	UL Dry Location Only
	Meets California Title 24 JA8-2016
	DC motor

P250074-31M-30



Contact:




Dimensions:

Diameter: 56 in Height: 18 in

White Opal Polycarbonate Light Cover

Width: 8 in Height: 4-3/4 in





Carrollwood

• Dry Location Only PROGRESS LED

Dimming Notes:

P250074-31M-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Eaton AAL06
IDevices IDEV009
Leviton 6681
Leviton 6672
Leviton 6674
Lutron NTEVL-300
Lutron DVELV-300P
Lutron DVCL-253P
Lutron AYCL-153P

Lutron TGCL-153-PH-WH Lutron MACL-153M

Lutron SCL-153P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P250074-31M-30