

Project:

Fixture Type:

Location:

Contact:

# Gillen

Ceiling downrod Mounted • Damp Location Listed PROGRESS LED

# **Description:**

Gillen 56" 4-Blade LED Indoor/Outdoor Matte Black Vintage Electric Ceiling Fan with Light Kit and Clear Glass Shade

### **Specifications:**

- · Clear Glass Bowl
- Canopy covers a standard 4" recessed outlet box: 6.625 in W., 2.25 in ht., 6.625 in depth
- · Hdwr. Included
- 80 in of wire supplied

#### **Performance:**

Input Power	7 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	600/85 (LM-79)
CCT	2700 K
CRI	80 CRI
Life (hours)	15000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime Warranty
Labels	UL Damp Location Listed
	DC motor

# P250075-31M-WB





## **Dimensions:**

Diameter: 56 in Height: 21-5/8 in

Clear Glass Bowl Width: 7-1/4 in Height: 6-1/2 in

