

Trevina V

Ceiling downrod Mounted • Dry Location Listed **PROGRESS LED**



Description:

Trevina V 52" 3-Blade Indoor Painted Nickel ENERGY STAR Modern Ceiling Fan with Light Kit and White Opal Shade

Specifications:

- White Opal Glass Bowl
- Canopy covers a standard 4" recessed outlet box: 5.875 in W., 2.5 in ht., 5.875 in depth
- Hdwr. Included
- 80 in of wire supplied

Performance:

Number of Lamps	2
Input Power	9 W per lamp (18 W total)
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	800/96 (LM-79) per lamp (1600 lm total)
CCT	3000 K
CRI	90 CRI
Life (hours)	25000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime Warranty
Labels	UL Dry Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016
	AC motor

P250076-152-WB



Dimensions:

Diameter: 52 in
 Height: 16-1/2 in

White Opal Glass Bowl
 Width: 9-1/4 in
 Height: 2-7/8 in

ENERGYGUIDE

**Estimated
Yearly Energy Cost**

\$8

\$3
\$34

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day
 • **Your cost depends on rates and use**
 • Energy Use: 29 Watts

Airflow

3,360

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
 • Airflow Efficiency: 116 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy