

Project:

Fixture Type:

Location:

Contact:

# Air Pro E-Star Fan

Ceiling downrod Mounted • Dry Location Listed PROGRESS LED



## **Description:**

Air Pro 52 in. Brushed Nickel 5-Blade ENERGY STAR Rated AC Motor Ceiling Fan with LED Light

### **Specifications:**

- · Etched White Polypropylene Shatter Resistant Diffuser
- · Dimmable to 10% brightness (See Dimming Notes)
- · Canopy covers a standard 4" recessed outlet box: 5 in W., 2.25 in ht., 5 in depth
- · Hdwr. Included
- 80 in of wire supplied

#### **Performance:**

Number of Lamps	4
Input Power	9 W
Input Frequency	60 Hz
CCT	3000 K
CRI	90 CRI
Life (hours)	25000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	30-year Limited Warranty
Labels	UL Dry Location Listed
	ENERGY STAR® qualified
	AC motor

# P250077-009-WB



# **Dimensions:**

Length: 52 in Diameter: 52 in Height: 18-11/16 in

Etched White Polypropylene Shatter Resistant Diffuser

