

Project:

Fixture Type:

Location:

Contact:

# Air Pro E-Star Fan

Ceiling downrod Mounted • Dry Location Listed PROGRESS LED



## **Description:**

Air Pro 52 in. White 5-Blade ENERGY STAR Rated AC Motor Ceiling Fan with Light

# **Specifications:**

- Etched White Polypropylene Shatter Resistant Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 5 in W., 2.25 in ht., 5 in depth
- Hdwr. Included
- + 80 in of wire supplied

## **Performance:**

| Number of Modules | 2                                  |
|-------------------|------------------------------------|
| Input Power       | 9 W                                |
| Input Frequency   | 60 HzCRI 90 CRI                    |
| Life (hours)      | 25000 (L70/TM-21)                  |
| EMI/RFI           | FCC Title 47, Part 15, Class B     |
| Warranty          | 30-year Limited Warranty           |
| Labels            | UL Dry Location Listed             |
|                   | ENERGY STAR <sup>®</sup> qualified |
|                   | AC motor                           |



P250078-030-WB

#### **Dimensions:**

Length: 52 in Diameter: 52 in Height: 16-11/16 in

Etched White Polypropylene Shatter Resistant Diffuser

