

Air Pro Builder Fan

Ceiling downrod Mounted • Dry Location Listed

Description:

Air Pro 52 in. Matte Black 5-Blade AC Motor Transitional Ceiling Fan

Specifications:

- Canopy covers a standard 4" recessed outlet box: 5 in W., 2.25 in ht., 5 in depth
- Hdwr. Included
- 80 in of wire supplied

Performance:

Input Frequency	60 Hz
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	30-year Limited Warranty
Labels	UL Dry Location Listed
	AC motor

P250080-31M



Dimensions:

Length: 52 in
 Diameter: 52 in
 Height: 12-1/2 in



Side A
Black

Side B
Rustic Charcoal

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$10

Cost Range of Similar Models (19" – 84")

\$3
\$34

• Based on 12 cents per kWh and 6.4 hours use per day
 • Your cost depends on rates and use
 • Energy Use: 36 Watts

Airflow

3,328

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
 • Airflow Efficiency: 93 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy

REVERSIBLE FAN BLADE FINISHES