

oject.
xture Type:
cation:

Air Pro E-Star Fan

Ceiling downrod Mounted • Dry Location Listed

Contact:



Description:

Air Pro 52 in. White 5-Blade ENERGY STAR Rated AC Motor Transitional Ceiling Fan

Specifications:

- Canopy covers a standard 4" recessed outlet box: 5 in W., 2.25 in ht., 5 in depth
- · Hdwr. Included
- 80 in of wire supplied

Performance:

Input Frequency	60 Hz
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	30-year Limited Warranty
Labels	UL Dry Location Listed
	ENERGY STAR® qualified
	AC motor

P250084-030



Dimensions:

Length: 52 in Diameter: 52 in Height: 12-1/2 in

