

## Air Pro E-Star Fan

Ceiling downrod Mounted • Dry Location Listed



### Description:

Air Pro 52 in. Matte Black 5-Blade ENERGY STAR Rated AC Motor Transitional Ceiling Fan with Light

### Specifications:

- Canopy covers a standard 4" recessed outlet box: 5 in W., 2.25 in ht., 5 in depth
- Hdwr. Included
- 80 in of wire supplied

### Performance:

Input Frequency	60 Hz
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	30-year Limited Warranty
Labels	UL Dry Location Listed
	ENERGY STAR® qualified
	AC motor

# P250084-31M



### Dimensions:

Length: 52 in  
 Diameter: 52 in  
 Height: 12-1/2 in

## ENERGYGUIDE

**Estimated  
Yearly Energy Cost**

**\$8**

\$3
\$34

Cost Range of Similar Models (19" – 84")


• Based on 12 cents per kWh and 6.4 hours use per day  
 • Your cost depends on rates and use  
 • Energy Use: 29 Watts

**Airflow**

**3,298**

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move  
 • Airflow Efficiency: 112 Cubic Feet Per Minute Per Watt



All estimates based on typical use, excluding lights

ftc.gov/energy