

Air Pro Fan

Ceiling downrod Mounted • Dry Location Listed

Description:

Air Pro 52 in. Matte Black 5-Blade AC Motor Transition-al Ceiling Fan with Light

Specifications:

- Canopy covers a standard 4" recessed outlet box: 5 in W., 2.25 in ht., 5 in depth
- Hdwr. Included
- 80 in of wire supplied

Performance:

Input Frequency	60 Hz
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	30-year Limited Warranty
Labels	UL Dry Location Listed
	AC motor

P250084-31M



Dimensions:

Diameter: 52 in
Height: 12-1/2 in

