

Air Pro Builder Fan

Ceiling downrod Mounted • Dry Location Listed **PROGRESS LED**

Description:

Air Pro 52 in. Brushed Nickel 5-Blade AC Motor Transitional Ceiling Fan with Light

Specifications:

- Clear Seeded Glass Cone
- Canopy covers a standard 4" recessed outlet box: 5 in W., 2.25 in ht., 5 in depth
- Hdwr. Included
- 80 in of wire supplied

Performance:

Number of Lamps	4
Input Power	8.5 W
Input Frequency	60 Hz
CCT	3000 K
CRI	80 CRI
Life (hours)	15000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	30-year Limited Warranty
Labels	UL Dry Location Listed AC motor

P250085-009-WB



Dimensions:

Length: 52 in
 Diameter: 52 in
 Height: 18-11/16 in

Clear Seeded Glass Cone
 Width: 11 in
 Height: 3-3/8 in

ENERGYGUIDE

**Estimated
Yearly Energy Cost**

\$10

\$3
\$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6.4 hours use per day
- **Your cost depends on rates and use**
- Energy Use: 36 Watts

Airflow

3,330

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 93 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy