

Project:

Fixture Type:

Location:

Contact:

Air Pro Builder Fan

Ceiling downrod Mounted • Dry Location Listed PROGRESS LED

Description:

Air Pro 52 in. Brushed Nickel 5-Blade AC Motor Transitional Ceiling Fan with Light

Specifications:

- Clear Seeded Glass Cone
- Canopy covers a standard 4" recessed outlet box: 5 in W., 2.25 in ht., 5 in depth
- Hdwr. Included
- + 80 in of wire supplied

Performance:


Number of Lamps	4
Input Power	8.5 W
Input Frequency	60 Hz
CCT	3000 K
CRI	80 CRI
Life (hours)	15000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	30-year Limited Warranty
Labels	UL Dry Location Listed
	AC motor



Dimensions:

Length: 52 in Diameter: 52 in Height: 18-11/16 in

Clear Seeded Glass Cone Width: 11 in Height: 3-3/8 in



P250085-31M-WB