

Trevina IV

Ceiling Mounted • Dry Location Listed

Description:

Trevina IV Collection 52 in. Three-Blade Painted Nickel Transitional Ceiling Fan with LED Light Kit

Specifications:

- Frosted White Acrylic Cylindrical
- Fully dimmable with dimmable bulbs
- Canopy covers a standard 4" recessed outlet box: 5.5 in W., 2 in ht., 5.5 in depth
- Mounting Bracket
- 80 in of wire supplied

Performance:

Number of Bulbs	2
Input Power	6 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens (Source)	500 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	15000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime Warranty
Labels	ETL Dry Location Listed AC motor

P250093-152-WB



Dimensions:

Diameter: 52 in
 Height: 13-13/16 in

Frosted White Acrylic Cylindrical
 Width: 8 in
 Height: 2-1/8 in



Walnut

Silver

ENERGYGUIDE

<p>Estimated Yearly Energy Cost</p> <h1 style="font-size: 2em; margin: 0;">\$9.0</h1> <p style="font-size: 1.2em; margin: 0;">\$3 \$34</p> <p style="font-size: 0.8em; margin: 0;">Cost Range of Similar Models (19" – 84")</p> <p style="font-size: 0.7em; margin: 0;">• Based on 12 cents per kWh and 6.4 hours use per day • Your cost depends on rates and use • Energy Use: 31 Watts</p>	<p>Airflow</p> <h1 style="font-size: 2em; margin: 0;">2,725</h1> <p style="font-size: 0.8em; margin: 0;">Cubic Feet Per Minute</p> <p style="font-size: 0.7em; margin: 0;">• The higher the airflow, the more air the fan will move • Airflow Efficiency: 88 Cubic Feet Per Minute Per Watt</p>
---	--

All estimates based on typical use, excluding lights ftc.gov/energy