

Upshur

Ceiling Mounted • Damp Location Listed **PROGRESS LED**

Description:

Upshur Collection 52 in. Matte Black Transitional Ceiling Fan with LED Light Kit

Specifications:

- Frosted White Acrylic Round
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 6.31 in W., 2.06 in ht., 6.31 in depth
- Mounting Bracket
- 80 in of wire supplied

Performance:

Number of Modules	1
Input Power	18 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,450/80.56 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	54000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime Warranty
Labels	ETL Damp Location Listed Meets California Title 24 JA8-2019
	AC motor

P250094-31M-30



Dimensions:

Diameter: 52 in
 Height: 13-11/16 in

Frosted White Acrylic Round
 Width: 6-7/8 in
 Height: 1-15/16 in

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$9.0

\$3 | | | \$34

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day
 • Your cost depends on rates and use
 • Energy Use: 34 Watts

Airflow

3,408

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
 • Airflow Efficiency: 102 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy

P250094-31M-30

Photometrics:

ELECTRICAL DATA	P250094-31M-30
Input Voltage	120/277 VAC
Input Frequency	60 Hz
THD	<20%
EMI/RFI	FCC Title 47, Part 15, Class B
Dimming	Yes*

Over-voltage, over-current, short-circuit protected

*See Dimming Notes for more information