

Freestone

Ceiling Mounted • Dry Location Listed

Description:

Freestone Collection 52 in. Five-Blade Brushed Nickel Transitional Ceiling Fan with LED lamped Light Kit

Specifications:

- Frosted White Acrylic Cylindrical Plastic
- Fully dimmable with dimmable bulbs
- Canopy covers a standard 4" recessed outlet box: 6.31 in W., 2.06 in ht., 6.31 in depth
- Mounting Bracket
- 80 in of wire supplied

Performance:

Number of Bulbs	2
Input Power	6.5 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1000/83.33 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	15000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime Warranty
Labels	ETL Dry Location Listed AC motor

P250095-009-WB



Dimensions:

Diameter: 52 in
 Height: 15 in

Frosted White Acrylic Cylindrical
 Width: 7-1/8 in
 Height: 3-5/16 in Plastic

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$10.0

\$3

↓

\$34

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day
 • Your cost depends on rates and use
 • Energy Use: 36 Watts

Airflow

3,236

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
 • Airflow Efficiency: 90 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy