

Bastrop

Ceiling Mounted • Damp Location Listed

Description:

Bastrop Collection 26 in. Three-Blade Brushed Nickel Transitional Ceiling Fan with 3 Speed Remote Control

Specifications:

- Canopy covers a standard 4" recessed outlet box: 6.31 in W., 2.06 in ht., 6.31 in depth
- Mounting Bracket
- 80 in of wire supplied

Performance:

Input Voltage	120 VAC
Input Frequency	60 Hz
Warranty	Limited Lifetime Warranty
Labels	ETL Damp Location Listed
	AC motor

P250096-009



Dimensions:

Diameter: 26 in
Height: 13-1/2 in

ENERGYGUIDE	
<p>Estimated Yearly Energy Cost</p> <p>\$3.0</p> <p>\$3 \$34</p> <p><small>Cost Range of Similar Models (19" – 84")</small></p> <p><small>• Based on 12 cents per kWh and 6.4 hours use per day</small></p> <p><small>• Your cost depends on rates and use</small></p> <p><small>• Energy Use: 11 Watts</small></p>	<p>Airflow</p> <p>1,108</p> <p><small>Cubic Feet Per Minute</small></p> <p><small>• The higher the airflow, the more air the fan will move</small></p> <p><small>• Airflow Efficiency: 100 Cubic Feet Per Minute Per Watt</small></p>
<small>All estimates based on typical use, excluding lights</small>	
<small>ftc.gov/energy</small>	