

Bastrop

Ceiling Mounted • Damp Location Listed

Description:

Bastrop Collection 26 in. Three-Blade Graphite Transitional Ceiling Fan with 3 Speed Remote Control

Specifications:

- Canopy covers a standard 4" recessed outlet box: 6.31 in W., 2.06 in ht., 6.31 in depth
- Mounting Bracket
- 80 in of wire supplied

Performance:

Input Voltage	120 VAC
Input Frequency	60 Hz
Warranty	Limited Lifetime Warranty
Labels	ETL Damp Location Listed
	AC motor

P250096-143



Dimensions:

Diameter: 26 in
 Height: 13-1/2 in

ENERGYGUIDE

**Estimated
Yearly Energy Cost**

\$3.0

\$3 | | | \$34

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day
 • Your cost depends on rates and use
 • Energy Use: 11 Watts

Airflow

1,108

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
 • Airflow Efficiency: 100 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights

ftc.gov/energy