

Bastrop

Ceiling Mounted • Damp Location Listed

Description:

Bastrop Collection 26 in. Three-Blade Matte Black Transitional Ceiling Fan with 3 Speed Remote Control

Specifications:

- Canopy covers a standard 4" recessed outlet box: 6.31 in W., 2.06 in ht., 6.31 in depth
- Mounting Bracket
- 80 in of wire supplied

Performance:

| | |
|-----------------|---------------------------|
| Input Voltage | 120 VAC |
| Input Frequency | 60 Hz |
| Warranty | Limited Lifetime Warranty |
| Labels | ETL Damp Location Listed |
| | AC motor |

P250096-31M



Dimensions:

Diameter: 26 in
Height: 13-1/2 in

ENERGYGUIDE

| | |
|---|--|
| <p>Estimated Yearly Energy Cost \$3.0</p> <div style="border: 1px solid black; width: 100px; margin: 5px auto; display: flex; justify-content: space-between; padding: 2px;"> \$3 \$34 </div> <p style="font-size: 8px; margin: 0;">Cost Range of Similar Models (19" – 84")</p> <p style="font-size: 8px; margin: 0;">• Based on 12 cents per kWh and 6.4 hours use per day • Your cost depends on rates and use • Energy Use: 11 Watts</p> | <p>Airflow 1,108 Cubic Feet Per Minute</p> <p style="font-size: 8px; margin: 0;">• The higher the airflow, the more air the fan will move • Airflow Efficiency: 100 Cubic Feet Per Minute Per Watt</p> |
|---|--|

All estimates based on typical use, excluding lights

ftc.gov/energy