

Shaffer II

Ceiling downrod Mounted • Damp Location Listed **PROGRESS LED**

Description:

Schaffer II Collection 56 in. Four-Blade Antique Nickel Modern Organic Ceiling Fan with Integrated LED Lamped Light and Natural Jute Accents

Specifications:

- Frosted White Glass Flat Round
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box
- Mounting Bracket
- 80 in of wire supplied

Performance:

Input Power	18 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,600/88 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	46000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime Warranty
Labels	UL Damp Location Listed
	Meets California Title 24 JA8-2019
	AC motor

P250097-081-30



Dimensions:

Diameter: 56 in
 Height: 15.5 in

Frosted White Glass Flat Round



Side A
Classic Walnut

Side B
Grey Weathered Wood

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$12

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day
 • Your cost depends on rates and use
 • Energy Use: 43 Watts

Airflow

4,244

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
 • Airflow Efficiency: 98 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy

P250097-081-30

Dimming Notes:

P250097-081-30 is designed to be compatible with many controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Eaton_AAL06

IDevices_IDEV009

Leviton_6681

Leviton_6672

Leviton_6674

Lutron_NTEVL-300

Lutron_DVELV-300P

Lutron_DVCL-253P

Lutron_AYCL-153P

Lutron_SCL-153P

Lutron_TGCL-153-PH-WH

Lutron_MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.