



Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P250098-129 Springer II

Springer II Collection 60-in Twelve-Blade Architectural Bronze Modern Farm-house Windmill Ceiling Fan

Category: Ceiling Fans
Finish: Architectural Bronze (Painted)
Construction:

Diameter.: 60 in
Height: 16-3/16 in

MOUNTING	ELECTRICAL	ADDITIONAL INFORMATION
Ceiling downrod	80 in of wire supplied	cULus Damp Location Listed
Mounting Bracket	120 VAC	Limited Lifetime Warranty
Canopy covers a standard 4" recessed outlet box	Switch Type: Push button	

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$6

\$3

\$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6.4 hours use per day
- Your cost depends on rates and use
- Energy Use: 21 Watts

Airflow

4,283

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 205 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy