



Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____



P250098-31M Springer II

Springer II Collection 60-in Twelve-Blade Matte Black Modern Farmhouse Windmill Ceiling Fan

Category: Ceiling Fans
Finish: Matte Black (Painted)
Construction:

Diameter.: 60 in
 Height: 16-3/166 in

MOUNTING	ELECTRICAL	ADDITIONAL INFORMATION
Ceiling downrod	80 in of wire supplied	cULus Damp Location Listed
Mounting Bracket	120 VAC	Limited Lifetime Warranty
Canopy covers a standard 4" recessed outlet box	Switch Type: Push button	

ENERGYGUIDE

**Estimated
Yearly Energy Cost**

\$6

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day
 • Your cost depends on rates and use
 • Energy Use: 21 Watts

Airflow

4,283

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
 • Airflow Efficiency: 205 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy