

## Bexar

Ceiling ctc Mounted • Dry Location Only **PROGRESS LED**

### Description:

Bexar Collection 54 in. Six Blade Matte Black Modern Farmhouse Ceiling Fan with Integrated LED Light

### Specifications:

- Frosted White Plastic Flat Round
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box
- Mounting Plate
- 12 in of wire supplied

### Performance:

Input Power	18 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,600/88 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	46000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime Warranty
Labels	UL Dry Location Only
	AC motor

# P250099-31M-30



### Dimensions:

Diameter: 54 in  
 Height: 11.5 in

Frosted White Plastic Flat Round



Side A  
Distressed Ebony

Side B  
Matte Black

## ENERGYGUIDE

**Estimated  
Yearly Energy Cost**

**\$11**

\$3

\$34

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day  
 • Your cost depends on rates and use  
 • Energy Use: 41 Watts

All estimates based on typical use, excluding lights

**Airflow**

**2,630**

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move  
 • Airflow Efficiency: 64 Cubic Feet Per Minute Per Watt

[ftc.gov/energy](http://ftc.gov/energy)

# P250099-31M-30

## Dimming Notes:

---

P250099-31M-30 is designed to be compatible with many controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

IDevices\_IDEV009

Leviton\_6681

Leviton\_6672

Leviton\_6674

Lutron\_NTEVL-300

Lutron\_DVELV-300P

Lutron\_DVCL-253P

Lutron\_AYCL-153P

Lutron\_SCL-153P

Lutron\_TGCL-153-PH-WH

Lutron\_MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.