



Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____



P250100-31M Brazas

Brazas Collection 56 in. Six-Blade Matte Black Transitional Ceiling Fan

Category: Ceiling Fans
Finish: Matte Black (Painted)
Construction:

Diameter: 56 in
 Height: 13 in

MOUNTING	ELECTRICAL	ADDITIONAL INFORMATION
Ceiling downrod	80 in of wire supplied	UL Damp Location Listed
Mounting Bracket	120 VAC	Limited Lifetime Warranty
Canopy covers a standard 4" recessed outlet box	Switch Type: Push button	Meets California Title 24 JA8-2019

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$5

\$3

|

|

\$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6,4 hours use per day
- Your cost depends on rates and use
- Energy Use: 19 Watts

Airflow

4,538

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 245 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy