

Schaal

Ceiling downrod Mounted • Damp Location Listed **PROGRESS LED**

Description:

Schaal Collection 52 in. Five-Blade Matte Black Coastal Ceiling Fan with Integrated LED Light

Specifications:

- Frosted White Plastic Drum Shade
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box
- Mounting Bracket
- 80 in of wire supplied

Performance:

Number of Modules	1
Input Power	18 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,600/88 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	46000 (L70/TM-21)
Warranty	Limited Lifetime Warranty
Labels	UL Damp Location Listed Meets California Title 24 JA8-2019 DC motor

P250101-31M-30



Dimensions:

Diameter: 52 in
 Height: 16 in

Frosted White Plastic Drum Shade



Side A
Matte Black

Side B
Rustic Charcoal

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$10

Cost Range of Similar Models (19" – 84")

\$3
\$34

• Based on 12 cents per kWh and 6.4 hours use per day
 • Your cost depends on rates and use
 • Energy Use: 37 Watts

Airflow

3,340

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
 • Airflow Efficiency: 89 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy

Dimming Notes:

P250101-31M-30 is designed to be compatible with many controls.

The following is a partial list of known compatible dimmer controls.

P250101-31M-30