

# Tarsus

Ceiling downrod Mounted • Dry Location Only **PROGRESS LED**

## Description:

Tarsas Collection 52 in. Five Blade Brushed Nickel Modern Ceiling Fan with Integrated CCT-LED Light

## Specifications:

- Frosted White Plastic Flat Round
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box
- Mounting Bracket
- 80 in of wire supplied

## Performance:

Input Power	20 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	2,000/80 (LM-79)
CCT	2700 K
	3000 K
	5000 K
CRI	80 CRI
Life (hours)	50000 (L70/TM-21)
Warranty	Limited Lifetime Warranty
Labels	UL Dry Location Only
	Meets California Title 24 JA8-2019
	DC motor

# P250102-009-CS



## Dimensions:

Diameter: 52 in  
 Height: 14-3/4 in  
 Frosted White Plastic Flat Round



## ENERGYGUIDE

Estimated  
Yearly Energy Cost

# \$11

Cost Range of Similar Models (19" – 84")

\$3
\$34

• Based on 12 cents per kWh and 6.4 hours use per day  
 • Your cost depends on rates and use  
 • Energy Use: 38 Watts

Airflow

# 3,545

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move  
 • Airflow Efficiency: 94 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy

**Dimming Notes:**

---

P250102-009-CS is designed to be compatible with many controls.

The following is a partial list of known compatible dimmer controls.

**P250102-009-CS**