

Tarsus

Ceiling downrod Mounted • Dry Location Only **PROGRESS LED**

Description:

Tarsas Collection 52 in. Five Blade Matte Black Modern Ceiling Fan with Integrated CCT-LED Light

Specifications:

- Frosted White Plastic Flat Round
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box
- Mounting Bracket
- 80 in of wire supplied

Performance:

Input Power	20 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	2,000/80 (LM-79)
CCT	2700 K
	3000 K
	5000 K
CRI	80 CRI
Life (hours)	50000 (L70/TM-21)
Warranty	Limited Lifetime Warranty
Labels	UL Dry Location Only
	Meets California Title 24 JA8-2019
	DC motor

P250102-31M-CS



Dimensions:

Diameter: 52 in
 Height: 14-3/4 in

Frosted White Plastic Flat Round

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$11

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6,4 hours use per day
 • Your cost depends on rates and use
 • Energy Use: 38 Watts

Airflow

3,545

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
 • Airflow Efficiency: 94 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy



Side A
Matte Black

Side B
Rustic Charcoal

Dimming Notes:

P250102-31M-CS is designed to be compatible with many controls.

The following is a partial list of known compatible dimmer controls.

P250102-31M-CS