

Dallam

Ceiling downrod Mounted • Dry Location Only **PROGRESS LED**

Description:

Dallam Collection 60 in. Six-Blade Matte Black Transitional Ceiling Fan with Integrated CCT-LED Light

Specifications:

- Frosted White Plastic Cylindrical
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box
- Mounting Bracket
- 80 in of wire supplied

Performance:

Input Power	20 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,700/84 (LM-79)
CCT	2700 K 3000 K 5000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
Warranty	Limited Lifetime Warranty
Labels	UL Dry Location Only Meets California Title 24 JA8-2019

DC motor



P250103-31M-CS



Dimensions:

Diameter: 60 in
 Height: 14 in

Frosted White Plastic Cylindrical

ENERGYGUIDE

**Estimated
Yearly Energy Cost**

\$6

\$3

▼

\$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6.4 hours use per day
- **Your cost depends on rates and use**
- Energy Use: 20 Watts

Airflow

4,062

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 201 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy

Dimming Notes:

P250103-31M-CS is designed to be compatible with many controls.

The following is a partial list of known compatible dimmer controls.

P250103-31M-CS