

Tompkins

Ceiling downrod Mounted • Damp Location Listed **PROGRESS LED**

Description:

Tompkins Collection 52 in. Five Blade Brushed Nickel Coastal Ceiling Fan with Integrated CCT-LED Light

Specifications:

- Clear Hammered Glass Bowl
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box
- Mounting Bracket
- 80 in of wire supplied

Performance:

Number of Modules	1
Input Power	24 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,900/80 (LM-79)
CCT	2700 K 3000 K 5000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
Warranty	Limited Lifetime Warranty
Labels	UL Damp Location Listed Meets California Title 24 JA8-2019 DC motor

P250104-009-CS



Dimensions:

Diameter: 52 in
 Height: 17 in

Clear Hammered Glass Bowl



Side A
American Walnut

Side B
Silver

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$11

\$3

\$34

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day
 • Your cost depends on rates and use
 • Energy Use: 38 Watts

Airflow

3,296

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
 • Airflow Efficiency: 86 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy

Dimming Notes:

P250104-009-CS is designed to be compatible with many controls.

The following is a partial list of known compatible dimmer controls.

P250104-009-CS